


$\phi \frac{1}{4}$ "  
Rod Frame



Lined Bottom and Sides with  
2 Mesh x .063" Welded Wire  
(.437" Openings, 76% Open Area)

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/16$ "  
ANGULAR:  $\pm 5$  DEG.  
TWO PLACE DECIMAL  $\pm 0.03$   
THREE PLACE DECIMAL  $\pm 0.015$

EST WGT  
6.0 lbs.  
MATERIAL  
304 Stainless Steel  
FINISH  
Natural

Rectangular Wire Mesh Basket:  
12Lx12Wx12H, 304 SS, 1/4 Rod  
Frame, No Handles, Mesh: 2 x .063

SIZE **B** DWG. NO.  
TMT-120120120-N02S

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS  
DRAWING IS THE SOLE PROPERTY OF  
THREE M TOOL. ANY REPRODUCTION IN  
PART OR AS A WHOLE WITHOUT THE  
WRITTEN PERMISSION OF THREE M TOOL  
IS PROHIBITED.