



Lined Bottom and Sides with  
4 Mesh x .063" Woven Wire  
(.187" Openings, 56% Open Area)

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/16"$   
ANGULAR:  $\pm 5$  DEG.  
TWO PLACE DECIMAL  $\pm 0.03$   
THREE PLACE DECIMAL  $\pm 0.015$

**Rectangular Wire Mesh Basket:**  
18Lx12Wx6H, 304 SS, 5/16 Rod Frame,  
Stacking Handles, Mesh: 4 x .063

**PROPRIETARY AND CONFIDENTIAL**

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

EST WGT  
10.2 lbs.  
MATERIAL  
304 Stainless Steel  
FINISH  
Natural

SIZE **B** DWG. NO.  
TMT-180120060-A04S

DO NOT SCALE DRAWING

SCALE: 1:6

SHEET 1 OF 1