



Lined Bottom and Sides with
8 Mesh x .047" Woven Wire
(.078" Openings, 39% Open Area)

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ± 1/16"
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ±0.03
THREE PLACE DECIMAL ±0.015

Rectangular Wire Mesh Basket:
18Lx12Wx6H, 304 SS, 5/16 Rod Frame,
Stacking Handles, Mesh: 8 x .047

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

EST WGT
10.7 lbs.
MATERIAL
304 Stainless Steel
FINISH
Natural

SIZE **B** DWG. NO.
TMT-180120060-A08S

DO NOT SCALE DRAWING

SCALE: 1:6

SHEET 1 OF 1