


$\phi \frac{5}{16}$ "
Rod Frame



Lined Bottom and Sides with
2 Mesh x .063" Welded Wire
(.437" Openings, 76% Open Area)

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL $\pm 1/16$ "
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ± 0.03
THREE PLACE DECIMAL ± 0.015

Rectangular Wire Mesh Basket:
18Lx12Wx6H, 304 SS, 5/16 Rod Frame,
No Handles, Mesh: 2 x .063

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

EST WGT
7.2 lbs.
MATERIAL
304 Stainless Steel
FINISH
Natural

SIZE **B** DWG. NO.
TMT-180120060-N02S

DO NOT SCALE DRAWING

SCALE: 1:6

SHEET 1 OF 1