


$\phi \frac{5}{16}$ "  
Rod Frame



Lined Bottom and Sides with  
30 Mesh x .012" Woven Wire  
(.021" Openings, 40% Open Area)

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/16$ "  
ANGULAR:  $\pm 5$  DEG.  
TWO PLACE DECIMAL  $\pm 0.03$   
THREE PLACE DECIMAL  $\pm 0.015$

**Rectangular Wire Mesh Basket:**  
18Lx12Wx6H, 304 SS, 5/16 Rod Frame,  
No Handles, Mesh: 30 x .012

EST WGT  
9.2 lbs.  
MATERIAL  
304 Stainless Steel  
FINISH  
Natural

SIZE **B** DWG. NO.  
TMT-180120060-N30S

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS  
DRAWING IS THE SOLE PROPERTY OF  
THREE M TOOL. ANY REPRODUCTION IN  
PART OR AS A WHOLE WITHOUT THE  
WRITTEN PERMISSION OF THREE M TOOL  
IS PROHIBITED.

DO NOT SCALE DRAWING

SCALE: 1:6

SHEET 1 OF 1