



Lined Bottom and Sides with
4 Mesh x .063" Woven Wire
(.187" Openings, 56% Open Area)

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL $\pm 1/16"$
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ± 0.03
THREE PLACE DECIMAL ± 0.015

Rectangular Wire Mesh Basket:
18Lx12Wx9H, 304 SS, 5/16 Rod Frame,
Stacking Handles, Mesh: 4 x .063

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

EST WGT
12.2 lbs.

MATERIAL
304 Stainless Steel

FINISH
Natural

SIZE **B** DWG. NO.
TMT-180120090-A04S

DO NOT SCALE DRAWING

SCALE: 1:6

SHEET 1 OF 1