


$\phi \frac{5}{16}$ "  
Rod Frame



Lined Bottom and Sides with  
2 Mesh x .063" Welded Wire  
(.437" Openings, 76% Open Area)

UNLESS OTHERWISE SPECIFIED:		<b>Rectangular Wire Mesh Basket:</b> 18Lx12Wx9H, 304 SS, 5/16 Rod Frame, No Handles, Mesh: 2 x .063	
DIMENSIONS ARE IN INCHES			
TOLERANCES:			
FRACTIONAL $\pm 1/16$ "		<b>SIZE</b> DWG. NO. <b>B</b> TMT-180120090-N02S	
ANGULAR: $\pm 5$ DEG.			
TWO PLACE DECIMAL $\pm 0.03$		SCALE: 1:6 SHEET 1 OF 1	
THREE PLACE DECIMAL $\pm 0.015$			
EST WGT	8.3 lbs.		
MATERIAL	304 Stainless Steel		
FINISH	Natural		
DO NOT SCALE DRAWING			

**PROPRIETARY AND CONFIDENTIAL**  
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.