


$\phi \frac{5}{16}$ "  
Rod Frame



Lined Bottom and Sides with  
30 Mesh x .012" Woven Wire  
(.021" Openings, 40% Open Area)

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/16$ "  
ANGULAR:  $\pm 5$  DEG.  
TWO PLACE DECIMAL  $\pm 0.03$   
THREE PLACE DECIMAL  $\pm 0.015$

**Rectangular Wire Mesh Basket:**  
18Lx12Wx9H, 304 SS, 5/16 Rod Frame,  
No Handles, Mesh: 30 x .012

**PROPRIETARY AND CONFIDENTIAL**

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

EST WGT  
10.9 lbs.

MATERIAL  
304 Stainless Steel

FINISH  
Natural

SIZE **B** DWG. NO.  
TMT-180120090-N30S

DO NOT SCALE DRAWING

SCALE: 1:6

SHEET 1 OF 1