



Lined Bottom and Sides with
8 Mesh x .047" Woven Wire
(.078" Openings, 39% Open Area)

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL $\pm 1/16"$
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ± 0.03
THREE PLACE DECIMAL ± 0.015

Rectangular Wire Mesh Basket:
18Lx18Wx6H, 304 SS, 5/16 Rod Frame,
Stacking Handles, Mesh: 8 x .047

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
THREE M TOOL. ANY REPRODUCTION IN
PART OR AS A WHOLE WITHOUT THE
WRITTEN PERMISSION OF THREE M TOOL
IS PROHIBITED.

EST WGT
13.5 lbs.
MATERIAL
304 Stainless Steel
FINISH
Natural
DO NOT SCALE DRAWING

SIZE **B** DWG. NO.
TMT-180180060-A08S

SCALE: 1:6

SHEET 1 OF 1