



Lined Bottom and Sides with 30 Mesh x .012" Woven Wire (.021" Openings, 40% Open Area)

UNLESS OTHERWISE SPECIFIED:  
 DIMENSIONS ARE IN INCHES  
 TOLERANCES:  
 FRACTIONAL ± 1/16"  
 ANGULAR: ± 5 DEG.  
 TWO PLACE DECIMAL ±0.03  
 THREE PLACE DECIMAL ±0.015

EST WGT 9.0 lbs.  
 MATERIAL 304 Stainless Steel  
 FINISH Natural

Rectangular Wire Mesh Basket:  
 18Lx18Wx6H, 304 SS, 5/16 Rod Frame,  
 Stacking Handles, Mesh: 30 x .012

SIZE **B** DWG. NO. TMT-180180060-A30S

**PROPRIETARY AND CONFIDENTIAL**  
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

DO NOT SCALE DRAWING

SCALE: 1:6

SHEET 1 OF 1