



Lined Bottom and Sides with
2 Mesh x .063" Welded Wire
(.437" Openings, 76% Open Area)

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ± 1/16"
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ±0.03
THREE PLACE DECIMAL ±0.015

Rectangular Wire Mesh Basket:
18Lx18Wx12H, 304 SS, 5/16 Rod Frame,
Stacking Handles, Mesh: 2 x .063

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

EST WGT
13.4 lbs.

MATERIAL
304 Stainless Steel

FINISH
Natural

SIZE **B** DWG. NO.
TMT-180180120-A02S

DO NOT SCALE DRAWING

SCALE: 1:7

SHEET 1 OF 1