


Lined Bottom and Sides with 30 Mesh x .012" Woven Wire (.021" Openings, 40% Open Area)



UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN INCHES
 TOLERANCES:
 FRACTIONAL ± 1/16"
 ANGULAR: ± 5 DEG.
 TWO PLACE DECIMAL ±0.03
 THREE PLACE DECIMAL ±0.015

EST WGT
 11.7 lbs.
 MATERIAL
 304 Stainless Steel
 FINISH
 Natural

DO NOT SCALE DRAWING

Rectangular Wire Mesh Basket:
 18Lx18Wx12H, 304 SS, 5/16 Rod Frame,
 Stacking Handles, Mesh: 30 x .012

SIZE **B** DWG. NO.
 TMT-180180120-A30S

SCALE: 1:7

SHEET 1 OF 1

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.