# **MOEN**<sup>®</sup>

#### DESCRIPTION

- Metal construction with various finishes identified by suffix
- Flexible supply lines with 3/8" compression fittings
- Includes non-metal push-down waste assembly
- Includes optional 3 hole deck plate (escutcheon)

#### OPERATION

- Lever style handles
- Temperature controlled by 100° arc of handle travel

#### **FLOW**

- Water usage is limited to these maximum flow rates as indicated by corresponding product markings
- 1.2 gpm max (4.5 L/min) at 60 psi

#### **CARTRIDGE**

- Ceramic disc technology
- Nonmetallic/nonferrous and stainless steel material

#### **STANDARDS**

- Third party certified at WaterSense®, ASME A112.18.1/ CSA B125.1, and all applicable requirements referenced therein including NSF 61/9 & 372
- Products marked with 1.2 gpm are compliant with California water efficiency regulations
- Complies with California Proposition 65 and with the Federal Safe Drinking Water Act
- ADA for lever handles

#### WARRANTY

- Lifetime limited warranty against leaks, drips and finish defects to the original homeowner
- 10 years warranty when used in a multifamily installation
- 5 years warranty when used in a commercial installation

Visit www.moen.com/support for complete details and limitations

## **Specifications**




### Mikah™

One-Handle Lavatory Faucet

MODELS: 84310 Series





**CRITICAL DIMENSIONS** DO NOT SCALE