# MOEN®

#### DESCRIPTION

- Power Boost<sup>™</sup> Spray Technology
- Reflex'" pulldown system offers smooth operation,
- easy movement and secure docking
- · Metal construction with various finishes identified by suffix
- Duralock<sup>®</sup> guick connect installation
- Pulldown spray with 68" braided hose
- Flexible supply lines with 3/8" compression fittings
- · High arc spout provides height and reach to fill or clean large pots while pulldown wand provides the maneuverability for cleaning or rinsing 360° rotating spout
- **OPERATION**

- · Lever style handle
- Temperature controlled by 100° arc of handle travel
- Operates with less than 5 lbs. of force
- · Operates in stream or spray mode in the docked or retracted position

#### FLOW

• Flow is limited to 1.5gpm (5.7 L/min) at 60 psi

#### CARTRIDGE

1255<sup>™</sup> Duralast<sup>™</sup> cartridge for Single-Handle Faucets

#### **STANDARDS**

- Third party certified to IAPMO Green, ASME A112.18.1/CSA B-125.1 and all applicable requirements referenced therein including NSF 61/9 & 372
- Meets CalGreen and Georgia SB370 requirements
- Complies with California Proposition 65 and with the Federal Safe Drinking Water Act
- ADA for lever handle
- The backflow protection system in this device consists of two independently operating check valves, a primary and a secondary which prevent backflow

#### WARRANTY

- Lifetime limited warranty against material or
- manufacturing defects to the original homeowner
- · 10 year limited warranty when used in a multifamily installation
- · 5 year limited warranty when used in a commercial installation

## Specifications




### Boman<sup>™</sup> Single Handle Pulldown Kitchen Faucet

MODELS: 87162 SERIES

#### NOTE: THIS FAUCET IS DESIGNED TO BE INSTALLED THROUGH 1, 2, 3 AND 4 HOLE, 1-1/2" (38mm) MIN. DIA. (1 HOLE FOR SOAP DISPENSER)





SYNDIAL 622

201666

B/16/2021