

RESIDENTIAL Preferred Parts®

The premium line of approved replacement parts.



Resistored Stainless Steel Heating Elements

Preferred Parts resistored stainless steel elements feature a low watt density design with an outer sheath of Incoloy® 800 to resist failure from "dry firing". Built in resistor helps prolong anode life for greater tank protection and longer working life.

SCREW-IN ELEMENTS

- **480V/2000W**, 9-1/2", LWD
SP10870GL (Single)
AP10870GL-3 (Bulk*: 50)
- **480V/3000W**, 12-5/8", LWD
SP10870JL (Single)
AP10870JL-3 (Bulk*: 50)
- **480V/4000W**, 16-1/4", LWD
SP10870LL (Single)
AP10870LL-3 (Bulk*: 50)
- **480V/4500W**, 17-1/2", LWD
SP10870ML (Single)
AP10870ML-3 (Bulk*: 50)
- **480V/5000W**, 19-1/8", LWD
SP10870NL (Single)
AP10870NL-3 (Bulk*: 50)
- **480V/6000W**, 19-1/8", LWD
SP10870QL (Single)
AP10870QL-3 (Bulk*: 50)
- **277V/2000W**, 9-1/2", LWD
SP10871GL (Single)
AP10871GL-3 (Bulk*: 50)
- **277V/3000W**, 12-3/8", LWD
SP10871JL (Single)
AP10871JL-3 (Bulk*: 50)
- **277V/4000W**, 16-1/4", LWD
SP10871LL (Single)
AP10871LL-3 (Bulk*: 50)
- **277V/4500W**, LWD
SP10871ML (Single)
AP10871ML-3 (Bulk*: 50)
- **277V/5000W**, 19-1/8", LWD
SP10871NL (Single)
AP10871NL-3 (Bulk*: 50)
- **277V/6000W**, 19-1/8", LWD
SP10871QL (Single)
AP10871-QL-3 (Bulk*: 50)
- **240V/2000W**, 9-1/2", LWD
SP10869GL (Single)
AP10869GL-5 (Bulk*: 50)
- **240V/2500W**, 9-15/16", LWD
SP10869HL (Single)
AP10869HL-5 (Bulk*: 50)
- **240V/3000W**, 12-3/8", LWD
SP10869JL (Single)
AP10869JL-5 (Bulk*: 50)
- **240V/3500W**, 13-1/2", LWD
SP10869KL (Single)
AP10869KL-5 (Bulk*: 50)
- **240V/4000W**, 16-1/4", LWD
SP10869LL (Single)
AP10869LL-5 (Bulk*: 50)
- **240V/4500W**, 15-1/2", LWD
SP10869ML (Single)
AP10869ML-5 (Bulk*: 50)
- **240V/4500W**, 13-1/2", MWD
SP10869MM (Single)
AP10869MM-5 (Bulk*: 50)
- **240V/5000W**, 19-1/8", LWD
SP10869NL (Single)
AP10869NL-5 (Bulk*: 50)
- **240V/5500W**, 13-1/2", HWD
SP10869PH (Single)
AP10869PH-5 (Bulk*: 50)
- **240V/6000W**, 19-1/8", LWD
SP10869QL (Single)
AP10869QL-5 (Bulk*: 50)
- **208V/2000W**, 9-1/2", LWD
SP10867GL (Single)
AP10867GL-3 (Bulk*: 50)
- **208V/3000W**, 12-5/8", LWD
SP10867JL (Single)
AP10867JL-3 (Bulk*: 50)
- **208V/4000W**, 16-1/4", LWD
SP10867LL (Single)
AP10867LL-3 (Bulk*: 50)
- **208V/4500W**, 17-1/2", LWD
SP10867ML (Single)
AP10867ML-3 (Bulk*: 50)
- **208V/5000W**, 19-1/8", LWD
SP10867NL (Single)
AP10867NL-3 (Bulk*: 50)
- **208V/6000W**, 19-1/8", LWD
SP10867QL (Single)
AP10867QL-3 (Bulk*: 50)
- **120V/1440W**, 7-11/16", HWD
SP10868LH (Single)
AP10868LH-5 (Bulk*: 50)
- **120V/1700W**, 13-1/2", LWD
SP10868KL (Single)
AP10868KL-5 (Bulk*: 50)
- **120V/2000W**, 9-1/2", LWD
SP10868GL (Single)
AP10868GL-5 (Bulk*: 50)

* Elements may be ordered in bulk. Box consists of 50 elements and 50 gaskets of the same part number.

HWD = High Watt Density
MWD = Medium Watt Density
LWD = Low Watt Density

To place your order call 1-800-621-5622; fax 1-800-535-9538