

Contemporary round 8" single-function rainhead, 1.75 gpm

Features

- Single-function rainhead
- MasterClean[™] sprayface features an easy-to-clean surface that withstands mineral buildup
- Optimized sprayface for maximum performance
- 1.75 gpm (6.6 lpm) maximum flow rate

Material

Solid-brass construction for durability and reliability

Technology

 Katalyst[™] air-induction technology infuses water with air, creating bigger drops for a more powerful spray

Installation

1/2 -14 NPT connection





Codes/Standards ASME A112.18.1/CSA B125.1 DOE - Energy Policy Act 1992 EPA WaterSense™ California Energy Commission (CEC)

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

- -


Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant [™] Polished Nickel
	BN	Vibrant [™] Brushed Nickel
	BV	Vibrant [™] Brushed Bronze
	BL	Matte Black
	2MB	Vibrant [™] Brushed Moderne Brass
	RGD	Vibrant Rose Gold
	TT	Vibrant Titanium
	VHR	



Contemporary round 8" single-function rainhead, 1.75 gpm K-13688-G





Technical Information

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum
flow:1.75 gal/min (6.6 l/min)
80 psi (5.5 bar)

Notes

For use with automatic compensating valves rated at 1.5 gal/min (5.7 l/min) or less. Install this product according to the installation instructions.

