



Wellcomme™ Ultra

Commercial toilet with Mach® Tripoint® flushometer
K-PR96053-T5D

Features

- Fixture and touchless flushometer combination is engineered for optimal performance
- Elongated bowl offers added room and comfort
- 2-1/8" (54 mm) fully glazed trapway
- 10" x 7" (254 mm x 178 mm) water surface
- 10" or 12" (254 or 305 mm) rough-in
- 1.6 gpf (6.0 lpf)
- Flush valve activation distance is factory-set
- No external flush volume adjustment ensures water conservation
- 24-hour automatic sentinel flush keeps trapway fresh
- Mechanical override enables flushometer to be used manually even during a power outage
- Chloramine and chlorine resistance on all rubber components exposed to waterway
- Locking stop cap provides protection against vandalism
- Powered by 1.5V AA lithium batteries
- For this combination, order K-96053 bowl and K-10TD00R10 flushometer

Material

- Vitreous china bowl
- Brass flush valve with durable polished brass finish

Technology

- Electronic infrared sensor with Tripoint® technology for accurate activation
- Designed to outperform competitors in bowl cleanliness and plug resistance

Installation

- Seat sold separately



Codes/Standards


ASME A112.18.1/CSA B125.1
ASME A112.19.2/CSA B45.1
ASSE 1037/ASME A112.1037/CSA B125.37
DOE - Energy Policy Act 1992

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



Wellcomme™ Ultra
Commercial toilet with Mach® Tripoint® flushometer
K-PR96053-T5D



Technical Information

- All product dimensions are nominal.
- Toilet type: Floor-mount
 - Waste Outlet: Floor
 - Bowl shape: Elongated
 - Flush type: Flushometer valve siphon
 - Spud size: 1 1/2, Inlet, Top
 - Trap passageway: 2-1/8" (54 mm)
 - Water surface size: 10" x 7" (254 mm x 178 mm)
 - Rim to water surface: 6" (152 mm)
 - Rough-in: 12" (305 mm)
 - Seat-mounting holes: 5-1/2" (140 mm)

Notes

Install this product according to the installation instructions.

Fixture Supply Requirements

- Min static pressure: 35 psi (241.3 kPa)
- Max static pressure: 80 psi (551.6 kPa)
- Min flowing pressure: 25 psi (172.4 kPa)

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com.

3-23-2023 23:36 - US/CA/MX

