

INSTALLATION INSTRUCTIONS BAR FAUCET

Model No's:

**8081, 8181, 8781, 8881, 8901, 9081,
9181, 9281, 9881, 1008, 1038, 1068,
1078, 1098, 1208, 1608, 1628, 1648,
1668, 1688, 1708, 1728, 938**



**Congratulations on the purchase
of your Newport Brass product,
an excellent choice, that will give you
years of quality service and enhance
the look and style of your home.**

Recommended Installation by a Professional Plumbing Contractor

Note: The use of petroleum base plumbers putty on our products will nullify the warranty. We recommend the use of clear silicone sealing materials.

1. Drill hole in mounting surface. Recommended deck hole $\text{Ø}1.25''$ not to exceed $\text{Ø}1.50''$.
2. Place O-ring on underside of faucet body. See Fig. 1.
3. Insert Hoses and Threaded Rod through hole in mounting surface. Threaded Rod to be oriented to the rear of faucet, toward the wall. See Fig. 1.
4. Place Gasket, Crescent and Nut onto Threaded Rod and tighten with a wrench. See Fig. 1.
5. Attach faucet 1/2 NPT Hoses to Risers and Water Supply Valves (not included). See Fig. 2
6. Turn on Water Supply Valves, remove Aerator and flush faucet of debris.
7. Check for leaks and make any final adjustments. Re-install Aerator when clear water flows from the faucet.

