

## **NEWPORT BATH**

**Showerhead** 

215

#### **Features**

- Solid brass construction
- Traditional styling
- 74 brass spray jets
- Brass nozzles for aesthetic appeal
- 1/2" NPT inlet pivot ball fitting (3/4" NPSM without pivot ball fitting)
- 9-1/8" (23.2 cm) showerhead diameter
- 1.8 gallons (6.7 liters) per minute maximum flow rate

### **Codes / Standards Compliance**

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- IPC
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations

### **Colors / Finishes**

• 10B: Oil Rubbed Bronze

• 15: Polished Nickel

• 15A: Antique Nickel

• 26: Polished Chrome

• Other: Refer to the Newport Brass catalog for additional color/finish options.



# Specified Model Model Description Colors / Finishes 215 Showerhead 10B 15 15A 26 Other

### Product Specification: Add "Color / Finish" suffix to Model number, below.

The Showerhead shall be of solid brass construction. Showerhead shall have a brass nozzle spray jet design incorporating 74 individual spray nozzles. Showerhead shall have a 1/2" NPT inlet fitting (3/4" NPSM when removing pivot ball fitting) and 9-1/8" (23.2 cm) showerhead diameter while operating at 1.8 gallons (6.7 liters) per minute maximum flow rate. Showerhead shall be Newport Brass Model 215/\_\_\_\_.

## **NEWPORT BATH**

### **Product Dimensions** (units are in inches)





