

23 671

EUROCUBE®

SINGLE HOLE SINGLE-HANDLE DECK MOUNT VESSEL SINK FAUCET 1.2 GPM

Pure Freude
an Wasser



STANDARD SPECIFICATION:

- GROHE SilkMove®
- GROHE StarLight®
- GROHE EcoJoy™
- GROHE QuickFix® installation
- 13 7/16" Faucet height
- 7 1/16" Spout reach
- 9 13/16" Aerator height
- Solid brass body
- Single loop handle
- 15 3/16" Nylon braided flex hoses
- CALGreen/CEC compliant
- 1.2gpm (WaterSense)
- Vessel sink pop-up drain (48 657) sold separately
- Vessel sink pop-up drain (48 656) sold separately
- Grid drain (28 951) sold separately



PRODUCT FEATURES:



-  GROHE StarLight®
-  GROHE SilkMove®
-  GROHE EcoJoy™
-  GROHE QuickFix®

CERTIFICATIONS:



- ADA
- WaterSense
- CEC Certified
- Low Lead Certified
- CALGreen Compliant
- Massachusetts Plumbing Board Approved
- Energy Policy Act of 1992
- NSF 61
- NSF 372
- CSA B125.1
- ASME A112.18.1
- Complies with lead plumbing laws

AVAILABLE FINISHES:

- 23671000**  GROHE StarLight® Chrome
- 23671A00**  Hard Graphite
- 23671EN0**  Brushed Nickel InfinityFinish™
- 23671GN0**  Brushed Cool Sunrise

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 07-06-2022

US
Tel: 1.630.582.7711 Fax: 1.630.582.7722
For the most current Specification Sheet,
go to www.grohe.us.

Canada
Tel: 1.888.644.7643 Fax: 1.905.366.2071
For the most current Specification Sheet,
go to www.grohe.ca.

PART OF **LIXIL**

23 671

EUROCUBE®

SINGLE HOLE SINGLE-HANDLE DECK
MOUNT VESSEL SINK FAUCET 1.2 GPM

*Pure Freude
an Wasser*



TECHNICAL DATA:

| | |
|------------------------------|------------------|
| Product Height | 340 mm |
| Product Length | 225 mm |
| Product Width | 55 mm |
| Fitting Spout Height | 250 mm |
| Fitting Spout Reach | 180 mm |
| Fitting Handle Height | 312 mm |
| GPM (Min)-GPM (Max) | 1.2 gal (US)/min |
| Fitting No of Holes Required | 1 |

