

NEWPORT BATH

Body Spray **2171**



Features

- Solid brass construction
- Traditional styling
- Single function spray
- Finished spray surface
- Ball and socket design having a range of 60 degrees
- 1/2" NPSM inlet fitting
- 1-7/8" (4.8 cm) Body Spray diameter
- 2.5 gallons (9.5 liters) per minute maximum flow rate

Codes / Standards Compliance

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- IPC
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations

Colors / Finishes

- 10B: Oil Rubbed Bronze
- 15: Polished Nickel
- 15S: Satin Nickel - PVD
- 26: Polished Chrome
- Other: Refer to the Newport Brass catalog for additional color/finish options.



Specified Model

| Model | Description | Colors Finishes |
|-------|-------------|--|
| 2171 | Body Spray | <input type="checkbox"/> 10B <input type="checkbox"/> 15 <input type="checkbox"/> 15S <input type="checkbox"/> 26 <input type="checkbox"/> Other |

Product Specification: Add size designator and "Color / Finish" suffix to Model number, below.

The Body Spray shall be of solid brass construction. Body Spray shall have a single function spray pattern incorporating a finished spray surface. Body spray shall have a 1/2" NPSM inlet fitting and 1-7/8" (4.8 cm) diameter while operating at 2.5 gallons (9.5 liters) per minute maximum flow rate. Body Spray shall be Newport Brass Model 2171/____.

2171

PRODUCT DIMENSIONS *(Units are in inches)*

