

CHESTERFIELD

Widespread Lavatory Faucet

1030

Features

- · Solid brass construction
- Brass valve bodies
- Quarter-turn washerless ceramic disc valve cartridges
- ADA compliant traditional lever handles
- Spout assembly with integral supply hoses
- Pop-up drain with tailpiece
- 3-5/16" (8.4 cm) spout height at outlet
- 6-15/16" (17.6 cm) spout reach (c-c)
- For 8" (20.3 cm) centers Maximum 20" (50.8 cm)
- 1.2 gallons (4.5 liters) per minute maximum flow rate





Codes / Standards Compliance

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- IPC
- NSF 61
- ADA
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations
- EPA WaterSense®

Colors / Finishes

10B: Oil Rubbed Bronze
15: Polished Nickel
15S: Satin Nickel - PVD
26: Polished Chrome

• Other: Refer to the Newport Brass catalog for additional color/finish options.

| Specified Model | | |
|-----------------|----------------------------|-------------------------------|
| Model | Description | Colors Finishes |
| 1030 | Widespread Lavatory Faucet | ☐ 10B ☐ 15 ☐ 15S ☐ 26 ☐ Other |

Product Specification: Add "Color / Finish" suffix to Model number, below.

The two-handle Widespread Lavatory Faucet shall be made of solid brass construction. Faucet shall incorporate a spout assembly with integral supply hoses and feature brass valve bodies with quarter-turn washerless ceramic disc valve cartridges. Faucet shall have a 1.2 gallon (4.5 liter) per minute maximum flow rate. Product shall be for 8" (20.3 cm) centers - Maximum 20" (50.8 cm). Product shall incorporate a 3-5/16" (8.4 cm) spout height at outlet and a 6-15/16" (17.6 cm) spout reach (c-c). Faucet shall include a pop-up drain with tailpiece and incorporate ADA compliant traditional lever handles. Widespread Lavatory Faucet shall be Newport Brass Model 1030/

1030

PRODUCT DIMENSIONS (Units are in inches)

