

# Eaton 3BR2442L150

Catalog Number: 3BR2442L150

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 150 A, D1, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 42 Circuits, 24 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	3BR2442L150
<b>UPC</b>	<b>Product Length/Depth</b>
786676441704	3.88 in
<b>Product Height</b>	<b>Product Width</b>
29.12 in	14.5 in
<b>Product Weight</b>	<b>Warranty</b>
28.2 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

No feed-thru lugs

### Type

Main lug

### Amperage Rating

150 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Mounting

Combination

### Number of circuits

42

### Number of spaces

24

### Phase

Three-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

208Y/120, 240V

### Wire size

#1 AWG-300 kcmil Cu/Al

### Box size

D1

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR  
NEMA 1, 120/240 VAC, 3 PHASE

### Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR2442L150

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

NEMA rating

NEMA 1

Number of wires

4



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)