

Eaton BABF1020

Catalog Number: BABF1020

Eaton BAB thermal magnetic circuit breaker, Classic replacement circuit breaker, 15 A, 10 kAIC at 120/240 V, Single-pole, 120/240 V, #14-8 AWG Cu/Al, BQL



General specifications

Product Name	Catalog Number
Eaton BAB thermal magnetic circuit breaker	BABF1020
	UPC
	786685405063
Product Length/Depth	Product Height
3.25 in	3.5 in
Product Width	Product Weight
0.875 in	0.2 lb
Warranty	Compliances
1 year	NFPA 72
	HACR Rated
Certifications	
UL Listed	

Physical Attributes

Circuit breaker type

BAB

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Bolt-on Fire Alarm Circuit Breaker

Wire size

#14-8 AWG Cu/Al

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Voltage rating

120/240 V

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Eaton Fire Alarm Circuit Breaker](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BABF1020](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)