

Eaton CCV2125X

Catalog Number: CCV2125X

Eaton Type CCV Tenant Main Circuit Breaker, Tenant main circuit breaker, 125 A, 10 kAIC, Two-pole, 120/240 V, #2/0 AWG-300 kcmil Cu/Al, CCV, Type ECC unit enclosures, Load side terminals

General specifications

Product Name	Catalog Number
Eaton CCV tenant main breaker	CCV2125X
UPC	Product Length/Depth
786685368405	8 in
Product Height	Product Width
5.5 in	4.5 in
Product Weight	Warranty
2.83 lb	Limited lifetime residential, 1 year commercial
Certifications	Catalog Notes
UL 489	Terminals-standard lugs (wire connectors) suitable for copper or aluminum wire.



Type

Tenant main circuit breaker

Amperage Rating

125 A

Voltage rating

120/240 V

Circuit breaker frame type

CCV

Terminals

Load

Used with

Type ECC Unit Enclosures

Interrupt rating

10 kAIC

Main circuit breaker

CCV

Wire size

#2/0 AWG-300 kcmil Cu/Al

Number of poles

Two-pole

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CCV2125X](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)