

Eaton GFTCB215

Catalog Number: GFTCB215

Eaton BR GFCI circuit breaker, Ground fault personnel protection circuit breakers, 15 A, 10 kAIC, Two-pole, 120/240 V, GFTCB, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

General specifications



Product Name

Eaton BR GFCI circuit breaker

Catalog Number

GFTCB215

UPC

786676025607

Product Length/Depth

4.5 in

Product Height

2 in

Product Width

2.75 in

Product Weight

0.7 lb

Warranty

10 year

Certifications

UL 943

UL 489

Catalog Notes

Meets Federal Spec Classification W-C375

Type

Ground fault personnel protection circuit breakers

Amperage Rating

15 A

Voltage rating

120/240 V

Trip Type

Common

Circuit protection

Ground fault circuit interrupter

Indicators

GFI

Interrupt rating

10 kAIC

Main circuit breaker

GFTCB

Wire size

#14-4 AWG

Number of poles

Two-pole

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - GFTCB215](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)