MOEN®

Specifications

DESCRIPTION

- PowerBoost[™] technology provides boosted water performance with a push of a button
- Metal construction with various finishes identified by suffix
- Reflex[™] pulldown system offers smooth operation, easy movement and secure docking
- Duralock[™] quick connect installation
- Pulldown spray with 68" braided hose
- 3/8" compression connections will accept standard ball nose connection for 3/8" tubing

OPERATION

- Lever style handle
- Operates with less than 5 lbs. of force
- Operates in stream or spray mode in the pulldown or retracted position

FLOW

• Flow is limited to 1.5 gpm (5.7 L/min) at 60 psi

CARTRIDGE

- 1255™ Duralast™ cartridge for Single-Handle Faucets
- Engineered polymers, non-ferrous and stainless steel materials

STANDARDS

- Third party certified to IAPMO Green, ASME A112.18.1/CSA B-125.1 and all applicable requirements referenced therein including NSF 61/9 & 372
- Meets CalGreen and Georgia SB370 requirements
- Complies with California Proposition 65 and with the Federal Safe Drinking Water Act
- The backflow protection system in this device consists of two independently operating check valves, a primary and a secondary which prevent backflow ADA for lever handle

WARRANTY

- Lifetime limited warranty against leaks, drips and finish defects to the original homeowner
- 10 year limited warranty when used in a multifamily installation
- 5 year limited warranty when used in a commercial installation
- Visit www.moen.com/support for complete details and limitations



Reves[™]


Single-Handle High Arc Pulldown Kitchen Faucet

MODELS: 87932 SERIES

NOTE: THIS FAUCET IS DESIGNED TO BE INSTALLED THROUGH 1, 2, 3 OR 4 HOLES, 1-1/2" (38mm) MIN. DIA. (1 HOLE FOR SOAP DISPENSER)

ADA 🗲

GREEN



CRITICAL DIMENSIONS DO NOT SCALE