

NEWPORT BATH

Features

- Solid brass construction
- Contemporary styling
- ADA compliant slide bar adjustment handle
- Multi-function engine with 3 spray modes
- Rubber nozzles facilitate easy cleaning
- Handshower incorporates twin back-check valves
- 1/2" NPT inlet elbow fitting
- 4" (10.2 cm) showerhead diameter
- 2.0 gallons (7.6 liters) per minute maximum flow rate

Codes / Standards Compliance

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- IPC
- ADA
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations

Colors / Finishes

- 10B: Oil Rubbed Bronze
- 15: Polished Nickel
- 15S: Satin Nickel - PVD
- 26: Polished Chrome
- Other: Refer to the Newport Brass catalog for additional color/finish options.

Handshower with Slidebar Set

280F



Specified Model

Model	Description	Colors Finishes
280F	Handshower with Slide bar Set	<input type="checkbox"/> 10B <input type="checkbox"/> 15 <input type="checkbox"/> 15S <input type="checkbox"/> 26 <input type="checkbox"/> Other

Product Specification: Add "Color / Finish" suffix to Model number, below.

The Handshower with Slidebar Set shall be of solid brass construction while incorporating a non-metallic handshower engine. Handshower with Slidebar Set shall have a multi-function shower engine with 3 spray modes incorporating rubber nozzles to facilitate easy cleaning. Handshower with Slidebar Set shall incorporate twin back-check valves within the handshower handle. Handshower with Slidebar Set shall incorporate a handshower holder mechanism that affords linear and rotational adjustments to the handshower. Handshower with Slidebar Set shall have a 1/2" NPT inlet fitting and 4" (10.2 cm) showerhead diameter while operating at 2.0 gallons (7.6 liters) per minute maximum flow rate. Handshower with Slidebar Set shall be Newport Brass Model 280F/_____.

