FAIRLYNN

Features

- Solid metal construction
- Brass valve bodies
- Quarter-turn washerless ceramic disc valve cartridges
- ADA compliant traditional lever handles
- Spout assembly with integral supply hoses
- Pop-up drain with tailpiece
- 3-13/16" (9.7 cm) spout height at outlet
- 5-3/8" (13.7 cm) spout reach (c-c)
- For 8" (20.3 cm) centers Maximum 20" (50.8 cm)
- 1.2 gallons (4.5 liters) per minute maximum flow rate

Codes / Standards Compliance

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- IPC
- NSF 61
- ADA
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations
- EPA Watersense

Widespread Lavatory Faucet

8000









Colors / Finishes

09: Old World Bronze15: Polished Nickel15S: Satin Nickel - PVD26: Polished Chrome

Specified Model		
Model	Description	Colors Finishes
8000	Widespread Lavatory Faucet	091515S26

Product Specification Add "Length Indicator and Color / Finish" suffix to Model number, below.

The two-handle Widespread Lavatory Faucet shall be made of solid metal construction. Faucet shall incorporate a spout assembly with integral supply hoses and feature brass valve bodies with quarter-turn washerless ceramic disc valve cartridges. Faucet shall have a 1.2 gallon (4.5 liter) per minute maximum flow rate. Product shall be for 8" (20.3 cm) centers - Maximum 20" (50.8 cm). Product shall incorporate a 3-13/16" (9.7 cm) spout height at outlet and a 5-3/8" (13.7 cm) spout reach (c-c). Widespread Lavatory Faucet shall be Newport 365 Model 8000/____.

8000

PRODUCT DIMENSIONS (Units are in inches)

