




Mechanical Dimensions: Inches [mm]

Tolerances ± 0.02 [0.5] Unless Otherwise Specified



Wire Gauge	Dim "A"
12AWG	52.6mm
14AWG	52.6mm
16AWG	52.1mm
18AWG	52.2mm
20AWG	52.3mm

Part Numbers Information



Wire Gauge	Max Amp.
12 AWG	30A
14 AWG	20A
16 AWG	15A
18 AWG	10A


Electrical Specifications

Voltage Rating	58V
Temperature Rating	-40°C ~85°C

Material Specifications

	For use with APS and ANS Low-Profile Miniature Blade Fuses
Body Material	Nylon with Glass Fiber (UL94V-0)
Contact Material	Brass
Wire Length	5"
Wire Type	UL 1015 rated to FT1
Ingress Protection	IP66
	For custom inquiries please contact the factory

Retail Pack: Inches [mm]



Rev	Date of issue	Revision Notes	Designed	Approved
H	09-25-2024	Updated Dim A	RC	OF