



# Furnace Installation & Maintenance Test Kit



**FREE** UEi TOOL BACKPACK!  
\$134.95 Value



**UEi Tool Backpack**

Install Kits are packed in this UEi Tool Backpack. Built rugged, waterproof base, two compartments with inner pocket options and includes D-clip.

**Furnace Applications**

Confirms:

- Manufacturer requirements to maintain warranty
- CFM via external static pressure test
- Gas flow pressure
- System is safe from gas leaks
- Proper high voltage to power supply and ground
- Low voltage meets wiring diagram requirements

**Kit Includes**

- Hi-Res Differential Manometer Static Pressure Kit (EM720SPKIT)
- True RMS Clamp Meter (DL579)
- Combustible Leak Detector (CD100A)
- Differential Folding Thermometer (PDT655)
- UEi Tool Backpack (AC550)



BACKED BY  
**UEI**  
QUALITY

1  
YEAR  
WARRANTY

TRUE RMS  
ACCURACY

SAFETY  
CETLus

### DL579 600A True-RMS Dual Display HVAC/R Clamp Meter

- 750/1000V AC/DC, 600A AC/DC
- AC/DC Microamps
- Low Z (impedance)
- Resistance
- Continuity/Diode Test
- Frequency/Duty Cycle
- 1-Year limited warranty

Safety Rated: CATIV 300V / CATIII 600V  
Certified by ETL to IEC 61010-1, 3rd edition



### CD100A Combustible Leak Detector

- Senses leading combustible (Natural Gas, Propane, etc), non-combustible and toxic gases
- < 50 ppm methane sensitivity
- Detects Propane-Based Refrigerants R290A and R600. Known as "Natural Refrigerants" or "Not in Kind".
- Audio and visual tic rate, fully adjustable
- 1-Year limited warranty



### EM720SPKIT Hi-Res Differential Manometer Static Pressure Kit

- Measure static pressure
- Temperature compensated
- ±80 InWC
- Measures in 11 scales
- High Resolution: 0.001" (-9.999 to +9.999 inchH2O)
- 1-Year limited warranty



### PDT655 Differential Folding Pocket Thermometer

- Large easy-to-read backlit display
- Large easy to use buttons
- Measures T1, T2, T1-T2
- Min/Max
- Built-in magnet
- 1-Year limited warranty



520KIT