

Flexible Steel Conduit

Coils

Features

- Corrosion resistant
- Smooth interior for easy wire pull through
- Easy to follow contours
- Crush resistant

Applications

- For use as an electrical raceway in close quarters requiring extra flexibility

Standard Material

- Steel construction

Standard Finish

- Hot dip galvanized zinc coating



Catalog Number	UPC	Size	Feet/Coil	Ship Case	Weight/Case	Inches			
						Inside Diameter Min.	Inside Diameter Max.	Outside Diameter Min.	Outside Diameter Max.
5200	80341	3/8"	100'	100'	15	.374	.376	.555	.571
5250	85482	3/8"	250'	250'	37	.374	.376	.555	.571
5201	80342	1/2"	100'	100'	21	.618	.634	.85	.866
5202	80343	3/4"	100'	100'	25	.827	.846	1.043	1.063
5203	80345	1"	100'	100'	45	1.039	1.059	1.28	1.299
5203C50	85524	1"	50'	50'	24	1.039	1.059	1.28	1.299
5204	82011	1-1/4"	50'	50'	24	1.319	1.343	1.512	1.535
5205	80346	1-1/2"	50'	50'	30	1.496	1.52	1.827	1.85
5205C25	85526	1-1/2"	25'	25'	16	1.496	1.52	1.827	1.85
5206	80347	2"	25'	25'	19	2.047	2.075	2.335	2.362
5207	80348	2-1/2"	25'	25'	26	2.52	2.559	2.913	2.953
5208	80349	3"	25'	25'	31	3.071	3.11	3.465	3.504
5209	80350	3-1/2"	25'	25'	34	3.504	3.551	3.909	3.957
5210	80351	4"	25'	25'	34	4.094	4.154	4.449	4.508