


LEVELING ADJUSTABLE HEIGHT ALUMINUM GANTRY - AHA-2-8-10-ALO

APPROX WEIGHT: 213.54 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS AHA-2-8-10-ALO

CAPACITY IS 2,000 LBS.

BASE WIDTH IS 64"

MAX OVERALL HEIGHT IS 136" *

I-BEAM SIZE IS 6" TALL WITH

3 5/16" FLANGE WIDTH

OVERALL I-BEAM LENGTH IS 96"

USABLE I-BEAM LENGTH IS 72 1/4"

LEVELING LEG HEIGHT IS INDIVIDUALLY ADJUSTED

UP TO 16" MAX. TO LEVEL CRANE

UNDER I-BEAM HEIGHT MAY BE ADJUSTED IN 6"

INCREMENTS USING THE 6 HOLES IN THE UPRIGHTS

ADJUSTABLE UNDER I-BEAM HEIGHT

92" MIN.

130" MAX. *

CRANE MAY BE TAKEN APART AND BUNDLED WITH

(2) INCLUDED STRAPS FOR EASY TRANSPORT

ALUMINUM CONSTRUCTION

SPECIAL FEATURES

NONE

DIMENSION TOLERANCE $\pm 1/4"$

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.
UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE

[] As drawn [] As marked

Signed: _____ Date: _____

Printed Name: _____

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:

VESTIL MANUFACTURING

DRAWN BY: MTS

DATE: 10/11/2019

REFERENCE: X

SCALE: 1:42

QUOTED LEAD TIME: X

QUOTE # X

P.O.# X

W.O.# X

SALES: X

FILE NAME:

28-007-418