


LEVELING ADJUSTABLE HEIGHT ALUMINUM GANTRY - AHA-4-10-8-ALO

APPROX WEIGHT: 286.30 lbs.
DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS AHA-4-10-8-ALO
CAPACITY IS 4,000 LBS.
BASE WIDTH IS 65 3/16"
MAX OVERALL HEIGHT IS 114 1/8" *
I-BEAM SIZE IS 8" TALL WITH
4 3/16" FLANGE WIDTH
OVERALL I-BEAM LENGTH IS 120"
USABLE I-BEAM LENGTH IS 96 1/4"
LEVELING LEG HEIGHT IS INDIVIDUALLY ADJUSTED
UP TO 16" MAX. TO LEVEL CRANE
UNDER I-BEAM HEIGHT MAY BE ADJUSTED IN 6"
INCREMENTS USING THE 6 HOLES IN THE UPRIGHTS
ADJUSTABLE UNDER I-BEAM HEIGHT
68 1/8" MIN.
106 1/8" MAX. *
CRANE MAY BE TAKEN APART AND BUNDLED WITH
(2) INCLUDED STRAPS FOR EASY TRANSPORT
ALUMINUM CONSTRUCTION

SPECIAL FEATURES

NONE

DIMENSION TOLERANCE $\pm 1/4"$

APPROVAL	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.	
	UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE	
	[] As drawn [] As marked	
	Signed: _____ Date: _____	
Printed Name: _____		
LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING		

DISTRIBUTOR'S NAME:		P.O.#
VESTIL MANUFACTURING		X
W.O.#	DATE: 10/11/2019	SALES: X
DRAWN BY: MTS	REFERENCE: X	FILE NAME:
QUOTED LEAD TIME: X	SCALE: 1:42	28-007-432
QUOTE # X		