



# ADJUSTABLE STEEL GANTRY CRANE - KNOCKDOWN - AHSN-4-15-12

APPROX WEIGHT: 889.94 lbs.  
DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\*

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



3D VIEW FOR REFERENCE ONLY

## STANDARD FEATURES

MODEL NUMBER IS AHSN-4-15-12  
CAPACITY IS 4,000 LBS.  
BASE WIDTH IS 77 1/2"  
MAX OVERALL HEIGHT IS 152 15/16"  
I-BEAM HEIGHT IS 8 1/8"  
I-BEAM FLANGE WIDTH IS 4"  
OVERALL I-BEAM LENGTH IS 179 3/4"  
USABLE I-BEAM LENGTH IS 149 3/4"  
ADJUSTABLE UNDER I-BEAM HEIGHT  
144 7/8" MAX  
90 7/8" MIN  
HEIGHT IS ADJUSTABLE IN 6" INCREMENTS  
CASTERS: (4) Ø8" X 3" WIDE PHENOLIC  
SWIVEL CASTERS WITH FOUR  
LOCKING POSITIONS

## SPECIAL FEATURES

NONE

DIMENSION TOLERANCE  $\pm 1/4"$

APPROVAL	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.	
	<b>UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE</b>	
	[ ] As drawn [ ] As marked	
	Signed: _____ Date: _____	
Printed Name: _____		

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:		P.O.#
VESTIL MANUFACTURING		X
W.O.#		X
DRAWN BY: DLS	DATE: 06/30/14	SALES: X
REFERENCE: X	SCALE: 1:44	FILE NAME:
QUOTED LEAD TIME: X	QUOTE # X	28-007-316