



# ADJUSTABLE STEEL GANTRY CRANE - KNOCKDOWN - AHSN-4-15-9

APPROX WEIGHT: 773.28 lbs.  
DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\*

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



3D VIEW FOR REFERENCE ONLY

## STANDARD FEATURES

MODEL NUMBER IS AHSN-4-15-9  
CAPACITY IS 4,000 LBS.  
BASE WIDTH IS  $59 \frac{5}{8}$ "  
MAX OVERALL HEIGHT IS  $117 \frac{1}{4}$ "  
I-BEAM HEIGHT IS  $8 \frac{1}{8}$ "  
I-BEAM FLANGE WIDTH IS 4"  
OVERALL I-BEAM LENGTH IS  $179 \frac{3}{4}$ "  
USABLE I-BEAM LENGTH IS  $149 \frac{3}{4}$ "  
ADJUSTABLE UNDER I-BEAM HEIGHT  
 $109 \frac{1}{8}$ " MAX  
 $73 \frac{1}{8}$ " MIN  
HEIGHT IS ADJUSTABLE IN 6" INCREMENTS  
CASTERS: (4)  $\phi 8$ " X 3" WIDE PHENOLIC  
SWIVEL CASTERS WITH FOUR  
LOCKING POSITIONS

## SPECIAL FEATURES

NONE

DIMENSION TOLERANCE  $\pm \frac{1}{4}$ "

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.  
**UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE**  
[ ] As drawn [ ] As marked

Signed: \_\_\_\_\_ Date: \_\_\_\_\_

Printed Name: \_\_\_\_\_

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:		P.O.#
VESTIL MANUFACTURING		X
W.O.#		
X		SALES:
X		X
DRAWN BY:	DLS	DATE:
		06/30/14
REFERENCE:	X	SCALE: 1:36
FILE NAME:		
28-007-314		
QUOTED LEAD TIME:	X	QUOTE #
		X