



ADJUSTABLE STEEL GANTRY CRANE - KNOCKDOWN - AHSN-4-20-16

APPROX WEIGHT: 1168.51 lbs.
DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



DIMENSION TOLERANCE $\pm 1/4"$

STANDARD FEATURES

MODEL NUMBER IS AHSN-4-20-16
CAPACITY IS 4,000 LBS.
BASE WIDTH IS 89 1/4"
MAX OVERALL HEIGHT IS 204 9/16"
I-BEAM HEIGHT IS 12 3/16"
I-BEAM FLANGE WIDTH IS 4"
OVERALL I-BEAM LENGTH IS 239 3/4"
USABLE I-BEAM LENGTH IS 209 3/4"
ADJUSTABLE UNDER I-BEAM HEIGHT
192 7/16" MAX
126 7/16" MIN
HEIGHT IS ADJUSTABLE IN 6" INCREMENTS
CASTERS: (4) $\varnothing 8"$ X 3" WIDE PHENOLIC
SWIVEL CASTERS WITH FOUR
LOCKING POSITIONS

SPECIAL FEATURES

NONE

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.
UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE

[] As drawn [] As marked

Signed: _____ Date: _____

Printed Name: _____

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:		P.O.#
VESTIL MANUFACTURING		X
W.O.#	DATE: 06/30/14	SALES: X
DRAWN BY: DLS	REFERENCE: X	FILE NAME:
QUOTED LEAD TIME: X	SCALE: 1:58	28-007-321
QUOTE # X		