

ADJUSTABLE STEEL GANTRY CRANE - KNOCKDOWN - AHSN-6-10-14 APPROX WEIGHT: 922.71 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACK

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON





DIMENSION TOLERANCE ± 1/4"

STANDARD FEATURES

MODEL NUMBER IS AHSN-6-10-14 CAPACITY IS 6,000 LBS.

BASE WIDTH IS 89 1/4"

MAX OVERALL HEIGHT IS 177"

I-BEAM HEIGHT IS 8 1/8"

I-BEAM FLANGE WIDTH IS 4"

OVERALL I-BEAM LENGTH IS 119 3/4"

USABLE I-BEAM LENGTH IS 89 3/4"

USABLE I-BEAM LENGTH IS 89 3/4" ADJUSTABLE UNDER I-BEAM HEIGHT

> 169" MAX 103" MIN

HEIGHT IS ADJUSTABLE IN 6" INCREMENTS

CASTERS: (4) Ø8" X 3" WIDE PHENOLIC

SWIVEL' CASTERS WITH FOUR LOCKING POSITIONS

SPECIAL FEATURES
NONE

	APPROVA-	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE [] As drawn [] As marked			
	┞┖	Signed:			Date:
		Printed Name:			
		LEAD TIME WILL STAR	RT UPON RE	CEIPT OF SIGNE	ED APPROVAL DRAWING
DISTRIBUTOR'S NAME:				P.O.# X	
VESTIL MANUFACTURING				IG	W.O.# X
DRAWN BY: DLS			DATE: 06/30/2014		SALES: X
reference: X				SCALE: 1:45	FILE NAME:

QUOTE #

28-007-323

QUOTED LEAD TIME: X