ADJUSTABLE STEEL GANTRY CRANE - KNOCKDOWN - AHSN-6-15-12 APPROX WEIGHT: 947.24 lbs. *** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON - 179 3/4"*-*10 1/8" - 149 3/4" – - 169 1/4" — 145" MAX 155 5/16" 91" MIN 3D VIEW FOR REFERENCE ONLY Ø 16" **DIMENSION TOLERANCE ± 1/4"** STANDARD FEATURES SPECIAL FEATURES I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS MODEL NUMBER IS AHSN-6-15-12 REPRESENTED SATISFIES DESIGN AND DIMENSION **NONE** REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CAPACITY IS 6,000 LBS. CONFIRM PRODUCT AND INSTALLATION BASE WIDTH IS 77 1/2" COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. UNITS REQUIRING APPROVAL DRAWINGS OR MAX OVERALL HEIGHT IS 155 5/16" 0 I-BEAM HEIGHT IS 10 1/8" MODIFIED ARE NON-RETURNABLE [] As drawn [] As marked I-BEAM FLANGE WIDTH IS 4" OVERALL I-BEAM LENGTH IS 179 3/4" Signed: USABLE I-BEAM LENGTH IS 149 3/4" Printed Name: ADJUSTABLE UNDER I-BEAM HEIGHT LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING DISTRIBUTOR'S NAME: 145" MAX W.O.# X VESTIL MANUFACTURING 91" MIN HEIGHT IS ADJUSTABLE IN 6" INCREMENTS DRAWN BY: DLS DATE: 07/22/2014 SALES: X CASTERS: (4) Ø8" X 3" WIDE PHENOLIC reference: X SWIVEL CASTERS WITH FOUR SCALE: 1:42 FILE NAME: LOCKING POSITIONS Quoted lead time: $_{ m Y}$ QUOTE # 28-007-328