


ADJUSTABLE STEEL GANTRY CRANE - KNOCKDOWN - AHSN-8-20-16

APPROX WEIGHT: 1420.30 lbs.
DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



DIMENSION TOLERANCE $\pm \frac{1}{4}"$

STANDARD FEATURES

MODEL NUMBER IS AHSN-8-20-16
CAPACITY IS 8,000 LBS.
BASE WIDTH IS $89 \frac{1}{4}"$
MAX OVERALL HEIGHT IS $205 \frac{1}{8}"$
I-BEAM HEIGHT IS $12 \frac{5}{16}"$
I-BEAM FLANGE WIDTH IS $6 \frac{1}{2}"$
OVERALL I-BEAM LENGTH IS $239 \frac{3}{4}"$
USABLE I-BEAM LENGTH IS $209 \frac{3}{4}"$
ADJUSTABLE UNDER I-BEAM HEIGHT
 $193" \text{ MAX}$
 $127" \text{ MIN}$
HEIGHT IS ADJUSTABLE IN 6" INCREMENTS
CASTERS: (4) $\varnothing 8" \times 3"$ WIDE PHENOLIC
SWIVEL CASTERS WITH FOUR
LOCKING POSITIONS

SPECIAL FEATURES

NONE

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.
UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE

☐ As drawn ☐ As marked

Signed: _____ Date: _____

Printed Name: _____

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:		P.O.#
VESTIL MANUFACTURING		X
DRAWN BY: DLS		W.O.#
DATE: 06/30/2014		X
REFERENCE: X	SCALE: 1:56	SALES: X
QUOTED LEAD TIME: X	QUOTE #	FILE NAME:
	X	28-007-345