


ADJ. STEEL GANTRY CRANE WITH DUAL TIRE PNEUMATIC CASTERS - AHS-4-15-12-PNU

APPROX WEIGHT: 1062.05 lbs.

(DOES NOT INCLUDE WEIGHT
OF POWER OR PACKAGING!!!)

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



DIMENSION TOLERANCE $\pm 1/4"$

STANDARD FEATURES

MODEL NUMBER IS AHS-4-15-12-PNU
CAPACITY IS 4,000 LBS.

BASE WIDTH IS 96 1/4"

MAX OVERALL HEIGHT IS 164 1/8"

I-BEAM HEIGHT IS 8 1/8"

I-BEAM WIDTH IS 4"

OVERALL I-BEAM LENGTH IS 179 3/4"

USABLE I-BEAM LENGTH IS 149 3/4"

ADJUSTABLE UNDER I-BEAM HEIGHT

102" MIN

156" MAX

HEIGHT IS ADJUSTABLE IN 6" INCREMENTS

(4) Ø 15 1/2" DUAL TIRE PNEUMATIC CASTERS

(SWIVEL WITH (4) LOCKING POSITIONS)

-PNU MODELS ARE 12" TALLER THAN STANDARD

AHS UNITS OF THE SAME HEIGHT DESIGNATION

DURABLE LIQUID PAINT BLUE FINISH

SPECIAL FEATURES

NONE

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.
UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE
[] As drawn [] As marked

Signed: _____ Date: _____

Printed Name: _____

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:

VESTIL MANUFACTURING

DRAWN BY: MTS

DATE: 01/29/2021

REFERENCE: X

SCALE: 1:62

QUOTED LEAD TIME: X

QUOTE # X

P.O.# X

W.O.# X

SALES: X

FILE NAME:

28-007-477