


STEEL PIPE SAFETY BOLLARD - BOL-42-4.5-RED

APPROX WEIGHT: 24.39 lbs.
DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



BLACK & RED
SAFETY STRIPES

Ø 4 1/2"

42"


5/8"

STANDARD FEATURES

MODEL NUMBER: BOL-42-4.5-RED
OVERALL WIDTH: 8"
OVERALL LENGTH: 8"
OVERALL HEIGHT: 42"
PIPE DIA: 4 1/2"
LAG DOWN MOUNTING PLATE: 5/8" x 8" x 8"
WITH MOUNTING SLOTS: 7/8" x 1 1/4"
FOR 3/4" DIA. ANCHOR BOLTS (SOLD SEPERATELY)
BLACK & RED SAFETY STRIPES
BLACK REMOVABLE TOP CAP
TOUGH BAKED IN POWDER COATED RED FINISH
ALL STEEL CONSTRUCTION
(ASTM A-36 MIN.) WITH
WELDING TO MEET AWS
WARNING: CHECK APPLICABLE STATE
& LOCAL LAWS FOR YOUR AREA

SPECIAL FEATURES

NONE



FOR INTERNAL USE ONLY
PROJECT SIGN OFF

SALES

ENG.

FAB.

POWER

DIMENSION TOLERANCE $\pm 1/4"$

A
P
P
R
O
V
A
L

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.
ALL SPECIAL UNITS ARE NON-RETURNABLE
[] As drawn [] As marked

Signed: _____ Date: _____

LEAD TIME WILL START UPON RECEIPT
OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:

VESTIL MANUFACTURING

P.O.# X

W.O.# X

DRAWN BY: TJM

DATE: 06/10/15

SALES: X

REFERENCE: X

SCALE: 1:8

FILE NAME:

QUOTED LEAD TIME: X

QUOTE # X

23-007-009-002