

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0002092118](#)  
**Status:** **Active**  
**Overview:** Standard .093" Pin and Socket Connectors  
**Description:** 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Tin (Sn) Plated Brass Contact, 18-22 AWG, Bag

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 11890000-TS-000 (PDF)</a>
<a href="#">Product Specification PS-02-09-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification PK-1190-003-001 (PDF)</a>	



**General**

Product Family	Crimp Terminals
Series	<a href="#">1380</a>
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">Standard .093" Pin and Socket Connectors</a>
Packaging Alternative	<a href="#">02092116 (Reel)</a>
Product Name	Standard .093"
Taxonomy	Crimp Terminals
UPC	800753746114

**Physical**

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.206/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22
Wire Size mm <sup>2</sup>	N/A

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

Engineering Number	1380-(P901)L
--------------------	--------------

**Reference - Drawing Numbers**

Packaging Specification	PK-1190-003-001
Product Specification	PS-02-09-001
Sales Drawing	SD-1380-X-001
Test Summary	11890000-TS-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[1380 Series](#)

**Use With**

[1619](#) Plug or Receptacle Housing, [1545](#) Plug or Receptacle Housing, [1396](#) Plug or Receptacle Housing, [1490](#) Plug or Receptacle Housing, [2629](#) Plug or Receptacle Crimp Housings, [1261](#) Plug or Receptacle Housing, [1292](#) Plug or Recept

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Insertion Tool for Standard .093" Pin and Socket Terminals	<a href="#">11020003</a>
Extraction Tool for Standard .093"	<a href="#">11030006</a>

Pin and Socket  
Terminals  
Extractor Tool [638240200](#)  
for .093 and  
HCS-125 Product  
Series  
Hand Crimp Tool for [638280900](#)  
Standard .093" Pin  
and Socket Crimp  
Terminals, 18 AWG  
Hand Crimp Tool [638281400](#)  
for .093" Pin and  
Socket Crimp  
Terminals, 22 AWG  
Hand Crimp Tool for [638281700](#)  
Standard .093" Pin  
and Socket Crimp  
Terminals, 20 AWG

This document was generated on 08/26/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**