

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008520131](#)
Status: **Active**
Overview:
Description: KK 396 Crimp Terminal 8818, 18-22 AWG, Reel, Phosphor Bronze Tin (Sn)

General

Product Family	Crimp Terminals
Series	8818
Application	Power
Crimp Quality Equipment	Yes
Overview	kk
Product Name	KK 396
Taxonomy	Crimp Terminals
UPC	800754247023

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.186/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.41mm max.
Wire Size AWG	18, 20, 22
Wire Size mm ²	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	8818-A(P909)
--------------------	--------------

Reference - Drawing Numbers

Packaging Specification	PK-2759-002-001
Product Specification	PS-08-50-001
Sales Drawing	SD-8818-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[8818 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hand Crimp Tool for	638280300
3.96mm Pitch KK	
Crimp Terminals,	
18-22 AWG	
Mini-Mac Applicator	638881100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION