

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0010013026](#)  
**Status:** **Active**  
**Overview:** [SPOX Connector System](#)  
**Description:** 5.08mm Pitch SPOX Crimp Terminal Housing, 2 Circuits, Natural

**Documents:**

[3D Model](#) [Product Specification PS-5197-001-001 \(PDF\)](#)  
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**Agency Certification**

CSA LR19980  
 UL E29179

**General**

Product Family Crimp Housings  
 Series [5197](#)  
 Application Signal, Wire-to-Board  
 Overview [SPOX Connector System](#)  
 Product Name SPOX  
 Taxonomy Connector Housings  
 UPC 800753612631

**Physical**

Circuits (maximum) 2  
 Color - Resin Natural  
 Flammability 94V-2  
 Gender Receptacle  
 Glow-Wire Capable No  
 Material - Resin Nylon  
 Net Weight 766.600/mg  
 Number of Rows 1  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface 5.08mm  
 Stackable No  
 Temperature Range - Operating -40° to +105°C

**Material Info**

Engineering Number 5197-02

**Reference - Drawing Numbers**

Product Specification [PS-5197-001-001](#)  
 Sales Drawing [SD-5197-N-020](#)



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5197 Series](#)

**Mates With**

[5281](#) , [5282](#)

**Use With**

[5194](#) , [5225](#)