

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010013056](#)
Status: **Active**
Overview: [SPOX Connector System](#)
Description: 5.08mm Pitch SPOX Crimp Terminal Housing, 5 Circuits, Natural

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-5197-001-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [5197](#)
 Application Signal, Wire-to-Board
 Overview [SPOX Connector System](#)
 Product Name SPOX
 Taxonomy Connector Housings
 UPC 800754209410

Physical

Circuits (maximum) 5
 Color - Resin Natural
 Flammability 94V-2
 Gender Receptacle
 Glow-Wire Capable No
 Material - Resin Nylon
 Net Weight 1920.400/mg
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 5.08mm
 Stackable No
 Temperature Range - Operating -40° to +105°C

Material Info

Engineering Number 5197-05

Reference - Drawing Numbers

Product Specification PS-5197-001-001
 Sales Drawing SD-5197-N-020



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[5197](#) Series

Mates With

[5281](#) , [5282](#)

Use With

[5194](#) , [5225](#)