

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010112073

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK 254 Crimp Housing, High Pressure, 7 Circuits, Natural



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-7879-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		Crimp Housings
Series		7880
Application		Signal, Wire-to-Board
Overview		KK Interconnect Systems
Product Name		KK 254
Taxonomy		Connector Housings
UPC		800753611931
Physical		
Circuits (maximum)		7
Color - Resin		Natural (White)
Flammability		94V-0
Gender		Receptacle
Glow-Wire Capable		No
Material - Resin		Nylon
Net Weight		0.686/g
Number of Rows		1
Packaging Type		Bag
Panel Mount		No
Pitch - Mating Interface		2.54mm
Pitch - Termination Interface		2.54mm
Stackable		No
Temperature Range - Operating		See Product Specification
Solder Process Data		
Lead-freeProcess Capability		N/A
Material Info		
Engineering Number		7880-7B
Reference - Drawing Numbers		
Product Specification		PS-7879-001
Sales Drawing		SD-7880-001, SD-7880-002

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per -	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

7880 Series

Mates With

KK254 PCB Headers [42375](#) , [42377](#) , [42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[7879](#) KK High Pressure Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION