

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010112143

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK 254 Crimp Housing, High Pressure, 14 Circuits, Natural

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-7879-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

7880

Application

Signal, Wire-to-Board

Overview

KK Interconnect Systems

Product Name

KK 254

Taxonomy

Connector Housings

UPC

800753611962

Physical

Circuits (maximum)

14

Color - Resin

Natural (White)

Flammability

94V-0

Gender

Receptacle

Glow-Wire Capable

No

Material - Resin

Nylon

Net Weight

1.372/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Stackable

No

Temperature Range - Operating

See Product Specification

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

7880-14B

Reference - Drawing Numbers

Product Specification

PS-7879-001

Sales Drawing

SD-7880-001, SD-7880-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

7880 Series

Mates With

KK254 PCB Headers [42375](#) , [42377](#) , [42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[7879](#) KK High Pressure Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION