

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010112163

Status:

Active

Overview:

[KK Interconnect Systems](#)

Description:

KK 254 Crimp Housing, High Pressure, 16 Circuits, Natural

Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[3D Model \(PDF\)](#)

[Product Specification PS-7879-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Overview

Product Name

Taxonomy

UPC

Crimp Housings

7880

Signal, Wire-to-Board

[KK Interconnect Systems](#)

KK 254

Connector Housings

800753619418

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Stackable

Temperature Range - Operating

16

Natural (White)

94V-0

Receptacle

No

Nylon

1.568/g

1

Bag

No

2.54mm

2.54mm

No

See Product Specification

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

7880-16B

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-7879-001

SD-7880-001, SD-7880-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

7880 Series

Mates With

KK254 PCB Headers [42375](#) , [42377](#) , [42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[7879](#) KK High Pressure Crimp Terminal

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION