

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0014562258

Status:

Active

Overview:

SL Modular Connectors

Description:

2.54mm Pitch SL Insulation Displacement Connector Assembly, Female, Single Row, Version G, Positive Lock, Wire Size 24 AWG, 0.76µm Gold (Au), 25 Circuits

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Packaging Specification PK-70873-0001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Comments

Component Type

Glow-Wire Capable

Overview

Product Name

Taxonomy

UPC

Ribbon Cable / Wire Trap Connectors

70400

Terminals Preloaded

Housing

No

SL Modular Connectors

SL

Connector Housings

800754216586

Physical

Circuits (Loaded)

Color - Resin

Durability (mating cycles max)

Entry Angle

Flammability

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

PCB Retention

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire/Cable Type

25

Black

50

Vertical

94V-0

Yes

Phosphor Bronze

Gold

Tin

Polyester Alloy

4.027/g

1

None

Tube

2.54mm

0.762µm

1.905µm

Yes

Yes

N/A

-40° to +105°C

IDT or Pierce

1.35mm max.

24

Discrete Wire, Ribbon Cable

Electrical


Current - Maximum per Contact

Voltage - Maximum

3.0A

250V

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

70400 Series

Mates With

Single Row Housing [70018](#) , [70107](#) Version A, [70107](#) Version B, [70543](#) , [70545](#) , [70553](#) , [70555](#)

Use With

[7307](#) Tinned 28AWG, [7767](#) Topcoat 28AWG, [24241](#) Tinned 26AWG, [8996](#) Topcoat 26AWG, [24226](#) Tinned 24AWG, [8997](#) Topcoat 24AWG, [24369](#) High Flex 26AWG, [24389](#) High Flex 24AWG

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
IDT Discrete	621000700
Handtool Module	

Engineering Number	704001214	Ribbon Cable Tool Kit, Press Not Included	<u>622016600</u>
Reference - Drawing Numbers			
Packaging Specification	PK-70873-0001-001		
Sales Drawing	SDA-70400-1191-1214-001		

This document was generated on 09/26/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION